


# RACK MOUNTED PRO PILOT CHASSIS DIMENSIONS



FOR CONNECTIONS TO THE STATIC AND PITOT PORTS  
 250 ID TYGON TUBING IS RECOMMENDED  
 MC MASTER CARR PART NUMBER 5114K21 OR EQUIVALENT

NOTE: THE CHASSIS ASSEMBLY MOUNTS INSIDE THE SLEEVE ASSEMBLY  
 THE SLEEVE ASSEMBLY MOUNTS TO THE INSTRUMENT PANEL STRUCTURE  
 THE PANEL CUTOUT SHOULD BE 6.2" X 1.9".  
 THE SLEEVE SHOULD BE INSTALLED SO THAT IT IS FLUSH AGAINST THE REAR  
 OF THE PANEL CENTERED ON THE PANEL OPENING.  
 THE DESIGN WILL ACCOMMODATE A PANEL THICKNESS OF UP TO 0.250"  
 THE AUTOPILOT IS INSTALLED AND REMOVED FROM THE FRONT OF THE PANEL  
 SO IT IS IMPORTANT TO ENSURE SERVICE LOOPS IN THE CABLE AND PITOT/STATIC  
 TUBING ALLOWS INSTALLATION USING THIS METHOD

